

**IMPLANTY PIERSI MONOBLOC® -SILICONE**  
**WYPEŁNIONE SILIKONOWYM SPOISTYM ŻELEM**  
**SoftOne**

*Teksturowane*

WYSOKI PROFIL				NISKI PROFIL			
NAZWA HANDLOWA	PROJEKCJA	ŚREDNICA	Objętość w ml A + /- 2.5%	NAZWA HANDLOWA	PROJEKCJA	ŚREDNICA	Objętość w ml A + /- 2.5%
GS - HP 085-095	29	74	95	GS -LP 125-125	25	90	125
GS -HP 105-110	31	76	110	GS -LP 130-130	25	92	130
GS -HP 125-125	32	81	125	GS -LP 140-140	28	92	140
GS -HP 130-130	34	84	130	GS -LP 150-150	28	94	150
GS -HP 140-140	35	86	140	GS -LP 160-155	28	99	155
GS -HP 150-150	35	87	150	GS -LP 170-160	29	99	160
GS -HP 160-165	35	91	165	GS -LP 180-170	29	102	170
GS -HP 170-170	36	93	170	GS -LP 190-175	29	105	175
GS -HP 180-185	36	96	185	GS -LP 200-190	30	105	190
GS -HP 190-190	36	99	190	GS -LP 210-205	31	106	205
GS -HP 200-195	36	100	195	GS -LP 220-210	31	110	210
GS -HP 210-205	37	101	205	GS - LP 240-235	31	113	235
GS -HP 220-210	37	102	210	GS - LP 260-240	31	116	240
GS -HP 230-235	38	103	235	GS - LP 280-270	31	125	270
GS -HP 250-240	38	106	240	GS - LP 300-275	31	127	275
GS -HP 270-250	39	108	250	GS -LP 320-315	32	131	315
GS -HP 290-275	39	111	275	GS - LP 340-320	35	125	320
GS -HP 300-285	40	112	285	GS - LP 370-335	35	131	335
GS - HP 320-290	40	115	290	GS - LP 400-395	36	134	395
GS - HP 340-320	42	118	320				
GS - HP 380-330	43	125	330				
GS - HP 390-360	44	126	360				
GS -HP 400-400	44	127	400				
GS - HP 450-430	45	133	430				
GS - HP 550-500	45	134	500				
GS - HP 600-530	48	135	530				

# IMPLANTY PIERSI MONOBLOC® -SILICONE

## WYPEŁNIONE SILIKONOWYM SPOISTYM ŻELEM SoftOne

### *Mikroteksturowane i gładkie*

WYSOKI PROFIL				NISKI PROFIL			
NAZWA HANDLOWA	PROJEKCJA	SREDNICA	Objętość w ml A +/- 2.5%	NAZWA HANDLOWA	PROJEKCJA	SREDNICA	Objętość w ml A +/- 2.5%
GS - HP 085-085	29	74	85	GS -LP 125-115	25	90	115
GS -HP 105-100	31	76	100	GS -LP 130-120	25	92	120
GS -HP 125-115	32	81	115	GS -LP 140-130	28	92	130
GS -HP 130-120	34	84	120	GS -LP 150-140	28	94	140
GS -HP 140-130	35	86	130	GS -LP 160-145	28	99	145
GS -HP 150-140	35	87	140	GS -LP 170-150	29	99	150
GS -HP 160-155	35	91	155	GS -LP 180-160	29	102	160
GS -HP 170-160	36	93	160	GS -LP 190-165	29	105	165
GS -HP 180-175	36	96	175	GS -LP 200-180	30	105	180
GS -HP 190-180	36	99	180	GS -LP 210-195	31	106	195
GS -HP 200-185	36	100	185	GS - LP 220-200	31	110	200
GS -HP 210-195	37	101	195	GS - LP 240-225	31	113	225
GS -HP 220-200	37	102	200	GS - LP 260-230	31	116	230
GS - HP 230-225	38	103	225	GS - LP 280-260	31	125	260
GS - HP 250-230	38	106	230	GS - LP 300-265	31	127	265
GS - HP 270-240	39	108	240	GS - LP 320-305	32	131	305
GS - HP 290-265	39	111	265	GS -LP 340-310	35	125*	310
GS - HP 300-275	40	112	275	GS - LP 370-325	35	131	325
GS - HP 320-280	40	115	280	GS - LP 400-385	36	134	385
GS -HP 340-310	42	118	310				
GS - HP 380-320	43	125	320				
GS - HP 390-350	44	126	350				
GS - HP 400-390	44	127	390				
GS -HP 450-420	45	133	420				
GS - HP 550-490	45	134	490				
GS -HP 600-520	48	135	520				

**IMPLANTY PIERSI MONOBLOC®-SILICONE XP**  
**WYPEŁNIONE SILIKONOWYM SPOISTYM ŻELEM SoftOne®**  
*Teksturowane- Mikroteksturowane- Gładkie*

<b>NAZWA HANDLOWA</b>	<b>ŚREDNICA (mm)</b>	<b>PROJEKCJA (mm)</b>	<b>OBJĘTOŚĆ (ml) À +/- 2,5%</b>
<b>GS-XP180-170</b>	92	40	170
<b>GS-XP200-185</b>	95	41	185
<b>GS-XP250-230</b>	103	44	230
<b>GS-XP280-265</b>	106	46	265
<b>GS-XP300-280</b>	109	47	280
<b>GS-XP320-300</b>	111	48	300
<b>GS-XP350-330</b>	115	50	330
<b>GS-XP400-380</b>	120	52	380
<b>GS-XP450-425</b>	125	54	425
<b>GS-XP500-485</b>	129	56	485
<b>GS-XP600-595</b>	137	59	595
<b>OS-XP700-695</b>	145	62	695

