

**ANATOMICZNE IMPLANTY PIERSI MONOBLOC®-SILICONE  
WYPEŁNIONE SILIKONOWYM SPOISTYM ŻELEM SoftOne**

***Teksturowane***

| <b>NAZWA<br/>HANDLOWA</b> | <b>SZEROKOŚĆ<br/>(mm)</b> | <b>WYSOKOŚĆ<br/>(mm)</b> | <b>PROJEKCJA<br/>(mm)</b> | <b>OBJĘTOŚĆ<br/>(ml) A +/- 2,5%</b> |
|---------------------------|---------------------------|--------------------------|---------------------------|-------------------------------------|
| <b>GS -AN 140-135</b>     | 98                        | 91                       | 34                        | 135                                 |
| <b>GS -AN 160-155</b>     | 102                       | 95                       | 34                        | 155                                 |
| <b>GS-AN 180-175</b>      | 106                       | 99                       | 37                        | 175                                 |
| <b>GS-AN 200-195</b>      | 110                       | 103                      | 38                        | 195                                 |
| <b>GS - AN 230-225</b>    | 115                       | 107                      | 40                        | 225                                 |
| <b>GS - AN 250-245</b>    | 119                       | 110                      | 41                        | 245                                 |
| <b>GS - AN 280-275</b>    | 123                       | 114                      | 43                        | 275                                 |
| <b>GS - AN 300-295</b>    | 126                       | 117                      | 44                        | 295                                 |
| <b>GS - AN 350-345</b>    | 132                       | 123                      | 46                        | 345                                 |
| <b>GS - AN 400-390</b>    | 139                       | 129                      | 48                        | 390                                 |
| <b>GS - AN 500-490</b>    | 149                       | 139                      | 52                        | 490                                 |

***Mikroteksturowane***

| <b>NAZWA<br/>HANDLOWA</b> | <b>SZEROKOŚĆ<br/>(mm)</b> | <b>WYSOKOŚĆ<br/>(mm)</b> | <b>PROJEKCJA<br/>(mm)</b> | <b>OBJĘTOŚĆ<br/>(ml) A +/- 2,5%</b> |
|---------------------------|---------------------------|--------------------------|---------------------------|-------------------------------------|
| <b>GS -AN 140-125</b>     | 98                        | 91                       | 34                        | 125                                 |
| <b>GS -AN 160-145</b>     | 102                       | 95                       | 34                        | 145                                 |
| <b>GS-AN 180-165</b>      | 106                       | 99                       | 37                        | 165                                 |
| <b>GS-AN 200-185</b>      | 110                       | 103                      | 38                        | 185                                 |
| <b>GS - AN 230-215</b>    | 115                       | 107                      | 40                        | 215                                 |
| <b>GS - AN 250-235</b>    | 119                       | 110                      | 41                        | 235                                 |
| <b>GS - AN 280-265</b>    | 123                       | 114                      | 43                        | 265                                 |
| <b>GS - AN 300-285</b>    | 126                       | 117                      | 44                        | 285                                 |
| <b>GS - AN 350-335</b>    | 132                       | 123                      | 46                        | 335                                 |
| <b>GS - AN 400-380</b>    | 139                       | 129                      | 48                        | 380                                 |
| <b>GS - AN 500-480</b>    | 149                       | 139                      | 52                        | 480                                 |